

Room Name | Specimen Reception/ Sort/ Preparation

Room Number: SPREC

Last modified	01/03/2016
Briefed Area	20.00
Remarks	
Occupancy	Up to 4 staff members, 3 seated workstations
Hours of Operation	<input checked="" type="checkbox"/> 0800 Hours - 1800 or 2000 hours
Acoustics	
Description or Special Requirements	A Reception area where specimens for analysis are received, sorted and held temporarily before despatch into laboratory areas. Additional Design Requirements: - Security shutters or glazing may be required

Room Fabrics

AusHFG code	Description	Material	Finish	Specification	Comments
1000	Floor finish	Vinyl	Standard slip resistant	Seamless, coved	to sort/ preparation area
1149	Floor finish	Carpet	90/10 Wool/ Nylon	Broadloom, 48 oz.	to front reception area
3000	Wall finish	Paint	Acrylic, washable		
3060	Wall finish	Vinyl	Prefinished	Splashback	to basin & sorting bench, tiles also acceptable
4030	Wall protection	Composite	Prefinished PVC	Corner guards to 900 AFFL	as required
5007	Ceiling - Plasterboard	Plasterboard	Paint	Bulkhead	optional
5060	Ceiling - Acoustic	Acoustic	Prefinished	Drop-in tiles, 600x1200	
9004	Door - 1100mm	Solid Core/ Glass	Paint	Single leaf, observation panel	910mm clear opening, lockable
6030	Cornice	Aluminium	Powdercoat	24mm shadow angle	
2000	Skirting	Vinyl	Prefinished	Floor vinyl coved, 150 mmH	to sort/ preparation area
2010	Skirting	Vinyl	Prefinished	Feather edged, 150 mmH	to front reception area

Fittings and Furniture

AusHFG code	Description	Group	Qty	Comments
FF-1050	Bench - laminate	1	1	sorting bench
FF-1110	Bench - laminate, writing	1	1	
FF-11465	Keyboard shelf - drop down	1	3	optional
FF-17250	Pedestal drawer unit - mobile, 660mmH	3	2	under bench
FF-17360	Pinboard - fabric covered	1	2	to upstand of reception desk and over workstation bench
FF-18550	Reception desk - laminate/ timber	1	1	with resinate/ laminate countertop
FF-18930	Roller shutter, manual	1	1	optional, may also use safety glass or 'Perspex/ Lexan' materials
FF-1950	Chair - ergonomic, high	3	1	
FF-20000	Shelving unit - adjustable	1	6	over sorting/ preparation area benches
FF-2100	Chair - ergonomic, office	3	2	

Room Name | Specimen Reception/ Sort/ Preparation

Room Number: SPREC

AusHFG code	Description	Group	Qty	Comments
FF-4410	Cupboard - under bench	1	1	under part bench
FF-4460	Cupboard - wall mounted	1	3	over part workstation bench
FF-6154	Dispenser - paper/ hand towel	2	1	to basin
FF-6156	Dispenser - soap	2	1	to basin
FF-5824	Waste bin - general	3	1	

Fixtures, Equipment and associated Services

AusHFG code	Description	Grp	Qty	Ele	Data	CdW	HtW	WmW	Tap	Dns	Gas	Comments
FE-11400	Computer - PC & monitor	3	3	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	flat screen
FE-27900	Incubator - laboratory	3	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	optional
FE-2800	Basin - handwash, Type B	1	1	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	
FE-41100	Printer - networked	3	1	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
FE-43500	Refrigerator	3	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	specimen holding
FE-54510	Telephone - handset, standard	3	1	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
FE-8900	Centrifuge	3	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	

Service Requirements

AusHFG code	Description	Comments
S-5000	Airconditioning	
S-6000	General fluorescent	
S-6030	Special: downlights	over bed/ trolley
S-6055	Special: task light, built in	under O/H cupboards

Services

AusHFG code	Description	Group	Qty	Comments
S-9000	GPO: Single	1	1	Bedhead low level, for electric bed
S-9001	GPO: Double	1	10	
S-1006	Voice / Data outlet: double	1	5	1 outlet for telephone
S-5000	Airconditioning	1	1	
S-6000	General fluorescent	1	1	
S-6200	Light switches	1	3	
S-6030	Special: downlights	1	1	over bed/ trolley

Room Name | Specimen Reception/ Sort/ Preparation

Room Number: SPREC

AusHFG code	Description	Group	Qty	Comments
S-6055	Special: task light, built in	1	2	under O/H cupboards
S-10005	Duress alarm	1	1	